Fully Threaded Studs Cont.

Fully Threaded Studs Cont.

Diameter - 5/8"
Thread Size - 11
Thread - Coarse

	Globally Sourced			Made in USA		Globally Sourced					
	A193 Grade B16	A193 Grade B7									A193 Grade B7M
	Plain					Zinc		Hot Dipped Galvanized	Blue Fluoropolymer	Clear Cadmium	Plain
	Without Nuts	With 2H Nuts	Without Nuts	With 2H Nuts	Without Nuts	With 2H Nuts	Without Nuts				
Length	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
3-3/4"	0186032	0133651	32872	0133651D	32872D	0188450	0155132	0186671	0121250	0120981	0180402
4"	0186033	0133652	32873	0133652D	32873D	0188451	0155133	0186672	0121251	0120982	0180403
4-1/4"	0186034	0133653	32874	0133653D	32874D	0188452	0155134	0186673	0121252	0120983	0180404
4-1/2"	0186035	0133654	32875	0133654D	32875D	0188453	0155135	0186674	0121253	0120984	0180405
4-3/4"	0186036	0133655	32806	0133655D	32806D	-	0155136	-	0121254	0120985	0180406
5"	0186037	0133656	32876	0133656D	32876D	0188455	0155137	0186676	0121255	0120986	0180407
5-1/4"	0186038	0133657	32807	-	32807D	0188456	0155138	-	0121256	0120987	0180408
5-1/2"	0186039	0133658	32877	0133658D	32877D	-	0155139	0186678	0121257	0120988	0180409
5-3/4"	0186040	0133659	32808	-	32808D	0188458	0155140	0186679	0121258	0120989	0180410
6"	0186041	0133660	32878	0133660D	32878D	0188459	0155141	0186680	0121259	0120990	0180411
6-1/4"	0186042	0133661	32879	0133661D	32879D	0188460	0155142	-	0121260	0120991	0180412
6-1/2"	0186043	0133662	32890	0133662D	32890D	0188461	0155143	-	0121261	0120992	0180413
6-3/4"	0186044	0133663	32889	-	32889D	-	0155144	-	0121262	0120993	0180414
7"	0186045	0133664	32880	-	32880D	-	0155145	0186684	0121263	0120994	0180415
7-1/4"	0186046	0133665	32881	-	32881D	0188464	0155146	-	0121264	0120995	0180416
7-1/2"	0186047	0133666	32888	-	32888D	0188465	0155147	0186686	0121265	-	0180417
7-3/4"	0186048	0133667	32887	-	32887D	-	0155148	0186687	-	-	0180418
8"	0186049	0133668	32882	-	32882D	0188467	0155149	0186688	-	-	0180419
8-1/4"	0186050	-	32883	-	32883D	-	0155150	-	-	-	0180420
8-1/2"	0186051	0136984	32884	-	32884D	-	0155151	0186690	-	-	0180421
8-3/4"	0186052	-	32885	-	32885D	-	0155152	-	-	-	0180422
9"	0186053	-	32886	-	32886D	-	0155153	0186692	-	-	0180423
9-1/4"	0186054	-	0120907	-	0120907D	-	0155154	-	-	-	0180424
9-1/2"	0186055	-	0120908	-	0120908D	-	0155155	-	-	-	0180425
9-3/4"	0186056	-	0120909	-	0120909D	-	0155156	-	-	-	0180426
10"	0186057	0136985	0120910	-	0120910D	-	0155157	0186696	-	-	0180427

Diameter - 3/4"
Thread Size - 10
Thread - Coarse

	Globally Sourced			Made in USA		Globally Sourced					
	A193 Grade B16	A193 Grade B7									A193 Grade B7M
	Plain					Zinc		Hot Dipped Galvanized	Blue Fluoropolymer	Clear Cadmium	Plain
	Without Nuts	With 2H Nuts	Without Nuts	With 2H Nuts	Without Nuts	With 2H Nuts	Without Nuts				
Length	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
2-1/4"	0186069	-	-	-	-	-	-	-	-	-	0180439
2-1/2"	0186070	-	-	-	-	-	-	-	-	-	0180440
2-3/4"	0186071	-	-	-	-	-	-	-	-	-	0180441
3"	0186072	0133669	32891	0133669D	32891D	-	0155158	0186697	-	-	0180442
3-1/4"	0186073	0133670	32892	-	32892D	0188477	0155159	-	0121277	0121007	0180443
3-1/2"	0186074	0133671	32893	0133671D	32893D	0188478	0155160	0186699	0121278	0121008	0180444
3-3/4"	0186075	0133672	32894	0133672D	32894D	0188479	0155161	-	0121279	0121009	0180445
4"	0186076	0133673	32895	0133673D	32895D	0188480	0155162	0186701	0121280	0121010	0180446
4-1/4"	0186077	0133674	32896	0133674D	32896D	0188481	0155163	0186702	0121281	0121011	0180447
4-1/2"	0186078	0133675	32897	0133675D	32897D	0188482	0155164	0186703	0121282	0121012	0180448
4-3/4"	0186079	0133676	32898	0133676D	32898D	0188483	0155165	0186704	0121283	0121013	0180449
5"	0186080	0133677	32899	0133677D	32899D	0188484	0155166	0186705	0121284	0121014	0180450
5-1/4"	0186081	0133678	32809	0133678D	32809D	0188485	0155167	0186706	0121285	0121015	0180451
5-1/2"	0186082	0133679	32900	0133679D	32900D	0188486	0155168	-	0121286	0121016	0180452
5-3/4"	0186083	0133680	32810	0133680D	32810D	0188487	0155169	0186708	0121287	0121017	0180453
6"	0186084	0133681	32901	0133681D	32901D	0188488	0155170	-	0121288	0121018	0180454
6-1/4"	0186085	0133682	32902	0133682D	32902D	0188489	0155171	-	0121289	0121019	0180455
6-1/2"	0186086	0133683	32811	0133683D	32811D	0188490	0155172	-	0121290	0121020	0180456
6-3/4"	0186087	0133684	32812	0133684D	32812D	0188491	0155173	-	0121291	0121021	0180457
7"	0186088	0133685	32903	-	32903D	0188492	0155174	-	0121292	0121022	0180458
7-1/4"	0186089	0133686	32904	0133686D	32904D	0188493	0155175	-	0121293	-	0180459
7-1/2"	0186090	0133687	32813	-	32813D	-	0155176	0186715	0121294	-	0180460
7-3/4"	0186091	0133688	32814	-	32814D	0188495	0155177	0186716	0121295	-	0180461
8"	0186092	0133689	32905	0133689D	32905D	0188496	0155178	0186717	0121296	0121026	0180462
8-1/4"	0186093	0133690	32906	-	32906D	-	0155179	-	0121297	-	0180463
8-1/2"	0186094	0133691	32815	-	32815D	-	0155180	-	0121298	0121028	0180464
8-3/4"	0186095	-	32816	-	32816D	0188499	0155181	-	0121299	0121029	0180465
9"	0186096	0133693	32907	-	32907D	0188500	0155182	-	0121300	0121030	0180466
9-1/4"	0186097	-	0120911	-	0120911D	-	0155183	-	0121301	-	0180467
9-1/2"	0186098	-	0120912	-	0120912D	-	0155184	-	0121302	0121032	0180468
9-3/4"	0186099	-	0120913	-	0120913D	-	0155185	-	0121303	0121033	0180469
10"	0186100	0136986	0120914	-	0120914D	-	0155186	0186725	0121304	0121034	0180470
10-1/4"	0186101	-	0120915	-	0120915D	-	0155187	-	-	-	0180471
10-1/2"	0186102	-	0120916	-	0120916D	-	0155188	-	-	0121036	0180472
10-3/4"	0186103	-	0120917	-	0120917D	-	0155189	-	-	-	0180473
11"	0186104	-	0120918	-	0120918D	-	0155190	0186729	-	-	0180474
11-1/4"	0186105	-	0120919	-	0120919D	-	0155191	-	-	-	0180475
11-1/2"	0186106	-	0120920	-	0120920D	-	0155192	-	-	-	0180476
11-3/4"	0186107	-	0120921	-	0120921D	-	0155193	-	-	-	0180477
12"	0186108	0136987	0120922	-	0120922D	-	0155194	0186733	-	-	0180478